



anasonic



View Places That You Couldn't **Even See Before BB-HCM705**

BB-HCM701 and BB-HCM705 are highly compact network cameras that are only about 60% of the size of existing model. Thanks to their compactness, these models are inconspicuous and blend in well with the installation surface. They can be mounted on walls as well as ceilings. A wall-mounted camera can offer a more natural view as compared to an overhead position because the viewing angle is closer to that from the human eye.

These cameras can help you to seize business opportunities with their capability to eliminate gaps in time and distance thereby contributing to "Zero Distance Management".

When You Can't Be There



Waiting room



School **Entrances**






Lobby



Panasonic network cameras.
It allows safe, smooth, economical
business management that is totally
free from conventional distance
and time limitations.



Achieving Zero Distance Management with a Variety of Functions





Capture

Megapixel Cameras (*BB-HCM705 only)

Mega pixel and higher image quality

Resolution has been improved to 1280 x 960 pixels, enabling rendering of finer detail. VGA (Video Graphics Array) quality has also been improved.

Megapixel image quality comparison of new and existing models






New model: BB-HCM705 (VGA)

2x2 Pixel Binning (*BB-HCM705 only)

2 x 2 pixel binning treats four adjacent pixels as one virtual pixel, thereby increasing camera sensitivity, and improving viewability in low light conditions

4-pixel summation function *This function cannot



be used with 1280 x 960 display resolution. *The ON/OFF setting of this function is fixed and cannot be automatically.

Image quality comparison





[with 4-pixel summation function ON] [standard mode]

BB-HCM705

Capture

Sound and Shock **Detection Function**

When the camera reacts to a sound or shock, camera temporarily saves or transfers the image.



Control

EX Zoom (*BB-HCM705 only)

Although not equipped with optical zoom, these models have an EX Zoom [EX is supposed to stand for "excellence"] function. This allows high image quality during VGA (Video Graphic Array) display with the use of 1280 x 960 pixel image.



This allows high image quality during VGA (Video Graphic Array) display.




Connect

Data transmission / H.264 adopted

The adoption of H.264/ACV has enabled reduction of data volume by more than 30% compared to MPEG-4 when transmitting data of the same image quality.

Comparison of data size



Installation

Highly compact

Models BB-HCM701/705 are about 60% of the size of existing model, BB-HCM527, and therefore much more compact. Thanks to their compactness, these models are inconspicuous and blend in well with the installation surface.



Ceiling Flush mount Bracket

These models can be flush-mounted on ceilings. Compact and ceiling-mountable, cameras blend in with the installation surface with minimum protrusion.



Part Names



*1 See 1.1 Understanding the Camera Indicator in the Troubleshooting Guide on the CD-ROM for indicator meaning.

Specifications [BB-HCM701/BB-HCM705]

Server Video Compression JI			Camera			Terminal		
Video Compression JI						reminat		
	JPEG (3 levels), MPEG-4, H.264		Zoom		3 x digital zoom	Interface	10Base-T/100Base-TX Ethernet RJ-45 connector x 1	
Video Resolution 12			Viewing Angle	Horizontal: 69°, vertical: 51°	Horizontal: 67°, vertical: 50°	External Input	External sensor input x 1	
Image Quality (JPEG Only) JF	JPEG (favor clarity, standard, favor motion)		Pan/Tilt Angle Pan: -10° to +10° (ceiling mount);			SD Memory Card Slot	Full size	
Frame Rate*2 M	Max. 30 frames/second			-52° to +52° (wall mount) Tilt: -57° to 0° (ceiling mount); - 57° to + 57	° (wall mount)	General		
[6	[640 x 480, 320 x 240, 192 x 144]		Digital pan/tilt*5	BB-HCM705 only		Operating Temperature	Operation: 0°C to +40°C (+32°F to +104°F)	
Security U	User ID / Password, SSL		Number of Pixels		CMOS sensor, 300,000 pixels		Storage: -10°C to +50°C(+14°F to +122°F)	
Supported Protocols	IPv4 / IPv6 Dual-Stack IPv4: TCP, UDP, IP, HTTP, FTP, SMTP, DHCP, DNS, ARP, ICMP, PDP3, NTP, UP-DFTM, SMTP Authentication, RTP, RTSP, RTCP, HTTPS IPv6: TCP, UDP, IP, HTTP, FTP, SMTP, DNS, ICMPv6, POP3, NDP, NTP, RTSP, RTCP, HTTPS		Focus	Fixed 0.5 m-infinity		Operating humidity	Operation: 20 % to 80 % (No Condensation)	
			Aperture		F2.0		Storage: 20 % to 90 % (No Condensation)	
			White Balance	Auto/manual/hold	12.0	Dimension (H x W x D)		
				Auto		Weight	250g (0.55 lb.)	240g (0.53 lb.)
			Exposure			Power supply	Operation AC adaptor(Model No. BB-HCA7A)	
			Illuminance	(in Color Night View mode: 0.04 to 100,000 lux)	in Color Night View model	,	input 100 - 120 V AC, 50/60 Hz Output 12V DC, 750 mA Operation AC adaptor (Model No. BB-HCA7E) input 100 - 240 V AC, 50/60 Hz Output 12V DC, 750 mA	
User Access Limit M	Max. 30 simultaneous accesses (max. 10 accesses with voice reception)							
				Screen brightness,				
				white balance: automatic/manual setting		PoE	PoE standard IEEE 802.3af-2003	
Buffered Image*3	About 1160 frames (320 x 240, standard image quality) with time display (when SD memory card is not inserted)		Audio	·		Consumption	When Using an Optional AC adaptor (Model No. BB-HCATA) AC adaptor (Model No. BB-HCATA) AC adaptor (Model No. BB-HCATA) About 3.2 W (Max 3.8 W) When Using an Optional AC adaptor (Model No. BB-HCATA) AC adaptor (Model No. BB-HCATA) AC adaptor (Model No. BB-HCATA)	When Using an Ontional
			Audio Communication	Camera to PC				
Message-Digest Algorithm H	HMAC-MD5, HMAC-SHA-1		Audio Play Method	Play with ActiveX				
Message Transfer Condition A	Alarm, timer, Motion Detection, Sound or Shock		Audio Compression					When Using an Optional
	SMTP*4, FTP, HTTP		Audio Bandwidth				About 3.3 W [Max. 3.9 W]	About 2.5 W (Max. 2.9 W)
Image Transfer Method SI			Audio Input	Built-in microphone			About 5.5 W (Max. 5.7 W)	

except H.264
Frame rate may slow down depending on the network environment, PC performance, image quality, SD memory recording, using IPsec or what object you view.

*4 POP before SMTP authentication and SMTP authentication (IPLAIN and LOISN) are supported. SMTP authentication (IRAM-MDS) is not supported.

*5 When [Max. Image Size] is set to [1280 X 960], zoom features are not available and digital pan/tilt features are also not available.

The maximum unber of frames changes depending on the image quality and what object you buffer.